

Zero in on a potential radioactive source quickly and more effectively with an RC2^{PLUS}

- Improved sensitivity and greater response
- Easy to use
- Larger high definition display with multiple languages
- Lightweight with longer battery life
- RC2^{PLUS} is available in two versions; Basic with Total Count version or the Advanced ROI Analysis version
- RadView software for integration



RC2^{PLUS}

HANDHELD RADIATION DETECTION SYSTEM

Durable and Dependable

The Basic RC2^{PLUS} automatically sets an alarm threshold over the total background count rate average upon each startup. This allows the RC2^{PLUS} to detect very low radiation levels even when hidden by shielding such as scrap metal, waste, or other dense material. The RC2^{PLUS} utilizes a large internal, high grade PVT scintillator to maximize sensitivity.

The Advanced RC2^{PLUS} utilizes both a PVT scintillator and a Geiger-Mueller tube to perform "Region Of Interest"(ROI) Analysis which allows the operator to see the distributed gamma energies in a histogram form. Once the ROI ranges are selected, a specific alarm threshold can be set for each ROI. This unique technology dramatically increases sensitivity while decreasing the adverse effects of "noise" caused by ambient background radiation. The RC2^{PLUS} provides many additional features such as Accumulated Dose Rate Alarm, Data Storage, and Graph Plotting.

Upgradable for Increased Flexibility

At any time the RC2^{PLUS} Basic can be easily upgraded to the RC2^{PLUS} Advanced. The RC2^{PLUS} Advanced stores operator results in a histogram record which can be downloaded via USB to RadComm's exclusive RadView software for further analysis. All reports can be saved in PDF format and archived for future reference. Remote servicing/diagnostics and potential future software updates of the RC2^{PLUS} can be achieved via an internet or network connection with RadComm's software application.

Upgradable for Radon Detection

New technology for express analyzing (< 5min) Radon concentration in air by using low energy resolution PVT plastic scintillator and high energy resolution Lanthanum Bromide inorganic scintillator as the gamma-detectors.

Size

- Detector Dimensions:
5.9" (15cm) H x 8.5" (21cm) L x 4" (10cm) W
- System weight: 3.4lbs (1.5kg)
- Detector case: Durable plastic with protective silicone sleeve

Electronics

- Integral PMT with EM shielding
- Audio & visual alarm with vibration
- Stable low noise, high voltage power supply
- Battery: Internal Lithium-Ion with charging LED indicator
- Micro-USB connector for battery charging and data transfer
- Battery Life: up to 20 hours continuous
- Battery Recharge Time:
 - Wall charger: 2.5 hrs
 - PC USB: 6 hrs (estimated)

Environmental

- Operating Temperature: -20°C (-4°F) to +60°C (140°F)
- Shock Resistance: Complies with ANSI N42.34

Display

- Backlit RGB colour LCD 320x240 resolution
- Viewing area: 3.5" (8.9cm) TFT LCD
- Basic: selectable units of measure: (CPS, μ Sv/h, μ R/r)
- Advanced: Histogram graph

Detector Specifications

- Basic & Advanced utilizes PVT:
- Size 4" (101.6mm) x 3" (76.2mm) x 2" (50.8mm)
- Advanced also includes: Geiger-Mueller tube
0.59" (12mm) x 1.9" (45mm), for high dose rate

Response/Sensitivity

- Energy Range: 15 KeV – 2.0 MeV
- Sensitivity: 8 cps/ μ Ci at 1m with CS137
- Gamma histogram: 256 Channels, channel capacity 16 bits
- Dose Rate Measurement Range: (With $\pm$ 30% of accuracy)
- 0.01 μ Sv/h ~ 0.1 mSv/h for Basic Model
- 0.01 μ Sv/h ~ 100 mSv/h for Advanced Model
- Accumulated Dose Alarm: Configurable

Software for Advanced Version

- Menu driven user interface
- Configurable data storage with backup
- E-mail capability (with network connection)

RC2^{PLUS} Basic vs Advanced

Each RC2^{PLUS} Package Includes:

- RC2^{PLUS} instrument charged and ready for use
- Hard shell carrying case
- Smart battery wall charger
- USB key with operation manual embedded
- Calibration certificate

Feature	Basic Option	Advanced Option
Search+Find	✓	✓
Total Counts	✓	✓
Dose Rate	✓	✓
Dose Rate Alarm		✓
Histogram		✓
Graph Plotting		✓
ROI Analysis		✓
ROI Alarm Threshold Settings		✓
Date Storage		✓
Accumulated Dose		✓
RadView Software		✓

RC2^{PLUS} - Docking Station (Optional)

- Docking Station charges RC2^{PLUS} instrument
- Provides area monitoring while the RC2^{PLUS} is docked
- Audio and visual alarm with reset button
- Wall mounted with security lock



Corporate Head Office

Scott Aikin
Saikin@radcommsystems.com
Jeff Adams
jadams@radcommsystems.com
2931 Portland Drive
Oakville, ON Canada L6H 5S4
Tel. +1 (905) 829-8290
Toll Free. 1 (800) 588-5229
Fax. +1 (905) 829-1406

USA

Joshua Hunter
jhunter@radcommsystems.com
602 E. Lincolnway Ave.
Valparaiso, IN USA 46383
Tel. +1 (773) 680-8430
Toll Free. 1 (800) 588-5229
Fax. +1 (219) 510-5764

Europe

Wim van Hove
wim.van.hove@radcomm europe.com
Watertorenweg 32, 2230 Herselt, Belgium
Tel. +32.14.75.02.13
Fax. +32.14.75.02.16

Black Sea

Osman Tureyyen
metkim@metkim.com
Kavacik, Onarimli Sokak
No 9 Altay Han
Daire: 8 Beykoz, Istanbul, Turkey
Tel. +90 (216) 425-1412
Fax. +90 (216) 425-1432

Latin America

Eduardo Ballesteros
analiticacontrol@prodginy.net.mx
Amatista No.27, El Pedregal
Atizapan de Zaragoza, 52948, Estado De Mexico
Tel. (52) 55 5077 4633/ (52) 55 3615 4910

India

Neelakshi Bhargava
neelakshi@radcommsystems.co.in
C-34, Ground Floor, Sawan Park, Ashok Vihar
New Delhi 110052, India
Tel. +91-9717671924
Fax. +91-9818650118